

# MD614

by Burndy  
Catalog ID: MD614

Prop 65 Notice

Hand Operated Tool With straight fiberglass handles 19 in long with grips, 4.5 ton Crimp Force, Permanent BG (5/8) and D3 grooves

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

5 year limited warranty



## Product Details

### General

|                      |                       |
|----------------------|-----------------------|
| Crimp Force Capacity | 4.5 ton               |
| Die Type             | W Dies                |
| Tool Type            | Hand Operated Crimper |
| Trade Name           | HYTOOL™               |
| Type                 | Crimpers              |
| UPC                  | 781810010945          |
| UPC 12 Digit         | 7818100109455         |

### Conductor Related

|                 |   |
|-----------------|---|
| Crimping Ranges | Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum |
|-----------------|---|

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)