

# MD64

by Burndy  
Catalog ID: MD64

Prop 65 Notice

Hytool, 31.50 in L, Weight-8lbs, forged steel jaw.

- Easy Die Insertion/Removal
- High Strength Forged Steel Jaws
- Spring loaded Positive Lock Die Retainer Buttons
- PTFE Impregnated Steel Backed Bronze Bushings
- Orange Alignment Grooves Provide Visual Check for Tool Adjustment
- High Strength Cast Aluminum
- Butting Jaws
- Permanent "O" Die Groove
- Permanent "D3" Die Groove

Features: Fiberglass Rated At 100 KV Per Foot For 5 Minutes, Permanent Dies: Yes, Covered Handles: Yes, Handle Length: 24 IN, Dies Used: BG And D3, Weight: 6 LB, Accepts Dies: Yes, Cutting Dies Available: Yes, Fully Covered: No 5 year limited warranty



## Product Details

### General

Application	For use on: Copper, Aluminum, ACSR, Copperweld, Alumoweld, Steel, 6201 5005, Compressed and compact conductors, Copper Taps: #10 sol. - 2/0 str., Aluminum, ACSR Taps: #14 sol. - 4/0 ACSR, Stirrups: #6 ACSR - 4/0 ACSR, Overhead Full Tension Deadend, Full Tension Splices, Non Tension Splices, and Terminals Conductor Range: #10 str. - 4/0 ACSR, Code conductor connectors: #6 - 4/0 str. Copper and Aluminum
Crimp Force Capacity	4.5 ton
Die Type	W and X styles
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810446058
UPC 12 Digit	7818104460588

### Dimensions

Length	31.5 in
Weight	8.25 lb
Width	7.50 in

### Conductor Related

Crimping Ranges	Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)