

# MD66

by Burndy  
Catalog ID: MD66

Prop 65 Notice

Hand Operated Tool, 25-3/8 in L, 9000 LBS, Weight: 6 lbs.

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Features: Ergonomically designed, one-piece, composite polymer handles, Comfort grip handles, Time-proven steel jaw designs, No tool adjustment required, 99,000 crimp/cycle life, Positive lock, spring loaded die retainer buttons, PTFE impregnated steel/bronze bushings and stainless steel pins, Electroless nickel plated jaws and jaw links5 year limited warranty



## Product Details

### General

Application	For Use On: Copper, Aluminum, ACSR, Copperweld, Alumoweld, Steel, 6201 5005, Compressed and compact conductors, Copper Taps: #10 sol. - 2/0 str., Aluminum, ACSR Taps: #14 sol. - 4/0 ACSR, Stirrups: #6 ACSR - 4/0 ACSR, Overhead Full Tension Deadend, Full Tension Splices, Non Tension Splices, and Terminals Conductor Range: #10 str. - 4/0 ACSR, Code conductor connectors: #6 - 4/0 str. Copper and Aluminum
Crimp Force Capacity	4.5 ton
Die Type	W and X styles
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810446102
UPC 12 Digit	7818104461022

### Dimensions

Length	24.50 in
Width	6.65 in

### Conductor Related

Crimping Ranges	Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)