



MD68HS60

by Burndy
Catalog ID: MD68HS60

Prop 65 Notice

MD6 Hotstick Tool, Forged Steel Crimping Jaws, Cast Al Frame, Fibre Glass Hotstick and Control rod, 68.19 IN L, 16.5 Lbs Weight, All Fiberglass Poles And Control Rod Tested To 100 KV Per Foot For 5 Min.

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Product Details

General

Die Type	W and X styles
Tool Type	Hot Stick
Type	Crimpers
UPC	781810446263
UPC 12 Digit	7818104462633

Dimensions

Length	68.19 in
Weight	16.5 lb

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)