



MD68HS72

by Burndy
Catalog ID: MD68HS72

Prop 65 Notice

MD6 Hotstick Tool, Forged Steel Crimping Jaws, Cast Al Frame, Fibre Glass Hotstick and Control rod, 80.19 IN L, 15.5 Lbs Weight, All Fiberglass Poles And Control Rod Tested To 100 KV Per Foot For 5 Min.

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Product Details

General

| | |
|--------------|----------------|
| Die Type | W and X styles |
| Tool Type | Hot Stick |
| Type | Crimpers |
| UPC | 781810446270 |
| UPC 12 Digit | 7818104462700 |

Dimensions

| | |
|--------|----------|
| Length | 80.19 in |
| Weight | 15.5 lb |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)