



## MD6AH48

by Burndy  
Catalog ID: MD6AH48

Prop 65 Notice

Straight handle Hot Stick Tool, Forged Steel Jaws, Heat Treated Al Frames, Fiberglass Handles, 13.75 Lbs Weight, 55.75 in L

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

## Product Details

### General

Die Type	W and X styles
Tool Type	Straight Handle Hot Stick
Type	Crimpers
UPC	781810446034
UPC 12 Digit	7818104460344

### Dimensions

Length	55.75 in
Weight	13.75 lb

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)