



MD6HS60

by Burndy
Catalog ID: MD6HS60

Prop 65 Notice

MD6 Hotstick Tool, Forged Steel Crimping Jaws, Cast Al Frame, Fibre Glass Hotstick and Control rod, 60 IN Handle L, 15.5 Lbs Weight

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Product Details

General

Die Type	W and X styles
Tool Type	MD6 Hot Stick
Type	Crimpers
UPC	781810446010
UPC 12 Digit	7818104460100

Dimensions

Length	69 in
Weight	15.5 lb

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)