

## MD6

by Burndy  
Catalog ID: MD6

Prop 65 Notice

Hand Operated Tool, 9000 lbs.

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

Features: Installs CABLELOK CRIMPIT And HYCRIMP Tap Connectors With One Additional Die Insert (W-O), Covered Handles: Yes, Permanent Dies: Yes, Handle Length: 25-3/8 IN, Weight: 6 LB, Dies Used: W O, Accepts Dies: Yes, Cutting Dies Available: Yes, Fully Covered: No5 year limited warranty



## Product Details

### General

Application	Crimping
Crimp Force Capacity	4.5 ton
Die Type	W & X dies
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810446003
UPC 12 Digit	7818104460033

### Dimensions

Length	25.38 in
Weight	6.25 lb
Width	7.04 in

### Conductor Related

Crimping Ranges	Copper: 10 sol. - 500 Kcmil; Copper Flex: #8 to 350 kcmil
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)