



MD734KIT1

by Burndy
Catalog ID: MD734KIT1

Prop 65 Notice

Hand-Operated POSI-PRESS™, Hand-operated tool with no ratchet mechanism with metal case and set of W-VT dies for #8 - 500 kcmil copper HYDENT™ and C-Taps for #12 - 3/0 AWG

- Ergonomically designed, one piece, composite polymer handles
- Comfort grip handles
- Time-proven forged steel jaw design
- No tool adjustment required
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Color Coded Dies
- Die index embossed on finished connection

5 year limited warranty

Product Details

General

Crimp Force Capacity	4.5 ton
Die Type	W-VT Dies
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimpers
UPC	781810052433
UPC 12 Digit	7818100524333

Dimensions

Length	25 in
Weight	7 lb
Width	8 in

Conductor Related

Crimping Ranges	Copper Lugs/Splices #8 - 500 kcmil, Copper Lugs/Splices #8 - 350 kcmil Flex, Copper Battery Lugs #8 - 350 kcmil Flex, Thin Wall C-Taps #12 - 3/0 AWG
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)