



MD734RKIT1

by Burndy
Catalog ID: MD734RKIT1

Prop 65 Notice

Full Stroke Ratchet Tool With Metal Case, Dies, 9000 Lbs At 60 Lbs Handle Force, #8 AWG-500 KCMIL Cu Hydent, 7 Lbs Weight.

- Full stroke ratchet mechanism
- Ergonomically designed one-piece composite polymer handles
- Comfort grip handles
- Time-proven forged steel jaw design
- No tool adjustment required
- Positive lock spring-loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Color coded dies
- Die index embossed on finished connection for inspectability

Includes: MD7-34R: 8 AWG - 500 KCMIL Cu HYDENT, Full Stroke Ratchet 5 year limited warranty

Product Details

General

Application	For Metal Carrying Case, And All Dies For 8 AWG - 500 KCMIL Copper, HYDENT And C-Taps
Crimp Force Capacity	4.5 ton
Die Type	W-VT Dies
Sub Brand	TOOLING ACCESSORY
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimpers
UPC	781810052440
UPC 12 Digit	7818100524400

Dimensions

Length	25 in
Weight	7 lb
Width	8 in

Conductor Related

Crimping Ranges	Copper Lugs/Splices #8 - 500 kcmil, Copper Lugs/Splices #8 - 350 kcmil Flex, Copper Battery Lugs #8 - 350 kcmil Flex, Thin Wall C-Taps #12 - 3/0 AWG
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)