



MD76

by Burndy
Catalog ID: MD76

Prop 65 Notice

Hand-Operated HYTOOL™, Installs full range of connectors #14 - 4/0, 4.5 ton Crimp force, Weight: 7 LB, Snub-nose, permanent D3 groove only

- Ergonomically designed, one-piece, composite polymer handles
- Comfort grip handles
- Time-proven steel jaw designs
- No tool adjustment required
- 99,000 crimp/cycle life
- Positive lock, spring loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Electroless nickel plated jaws and jaw links

5 year limited warranty

Product Details

General

Crimp Force Capacity	4.5 ton
Die Type	W and X styles
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimpers
UPC	781810010921
UPC 12 Digit	7818100109211

Dimensions

Length	25 in
Weight	7 lb
Width	8 in

Conductor Related

Crimping Ranges	Taps: Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups: #6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals: #10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations: #8 to 500 kcmil Copper Stranded, #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)