

# N2D67539T12

by Burndy  
Catalog ID: N2D67539T12

Copper Stud Connectors



## Product Details

### General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Studs
UPC	621945124110
UPC 12 Digit	6219451241100

### Dimensions

Dimension - B Length inch	2.31 in
Dimension - Pin Diameter fraction	1-3/4 in
Dimension - Pin Diameter inch	1.75 in
Dimension - Threads per inch	12

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)