

NA18A4N45

by Burndy
Catalog ID: NA18A4N45

Prop 65 Notice

Aluminium terminal, 5/8 in aluminium hex bolt, alum nut & galvanized split lock washers(4 places), 4 hole 0.56 dia each



Product Details

General

Application	Substation
Clamping Element Design	Body and Cap
Connector Type	Terminal
Installation Torque Recommended in-lb	480 LBS/in
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	3 x 3 - 4 holes
Physical Attribute - Pad Orientation	45 Degree
Plated	N
Plating Type	Unplated
UPC	781810234563
UPC 12 Digit	7818102345633

Dimensions

Connector Angle	45 Degree (pad to bolt axis)
Dimension - B Length inch	4.25 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - G inch	2.05 in
Dimension - Height inch	7.35 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in dia
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	4.47 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Width inch	4.5 in
Dimension - Width mm	114 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube EH Size	2" IPS tube
Conductor - AL Tube Std Size	2 IPS
Conductor - AL Tube Std Size Range	2 IPS
Conductor - Connection Combination	Tube to Flat
Conductor - Copper Tube Std Size	2 IPS IPS
Conductor - Copper Tube Std Size Range	2 IPS IPS
Conductor Type	<ul style="list-style-type: none">• AL Tube Std-Size• CU Tube Std-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)