



## NQ10M250D

by Burndy  
Catalog ID: NQ10M250D

Prop 65 Notice

Yellow Female Disconnect, #12 - 10 AWG

### Product Details

#### General

|                 |                 |
|-----------------|-----------------|
| Connector Type  | Male Disconnect |
| Insulation      | Y               |
| Insulation Type | Nylon           |
| Material        | Brass           |
| Plated          | Y               |
| Plating Type    | Tin             |
| Trade Name      | FINGRIP™        |
| UPC             | 781810020746    |
| UPC 12 Digit    | 7818100207466   |

#### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - D inch              | 0.35 in |
| Dimension - Length Overall inch | 1.14 in |
| Dimension - N inch              | 0.18 in |
| Dimension - Pad Width inch      | 0.25 in |

#### Conductor Related

|                                   |               |
|-----------------------------------|---------------|
| Conductor - Copper Str Size       | 12 AWG;10 AWG |
| Conductor - Copper Str Size Range | 12 AWG-10 AWG |
| Conductor Type                    | CU C Str-Size |

#### Certifications and Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |        |
|-----------------------|--------|
| Carton Quantity       | 600 EA |
| Minimum Pack Quantity | 50     |

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)