



## NS1515

by Burndy  
Catalog ID: NS1515

Prop 65 Notice

Cast Cu Alloy Bolted Coupler, 1" IPS, Silicon Bronze H/W

## Product Details

### General

Application	Substation
Connector Type	Couplers
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810002537
UPC 12 Digit	7818100025377

### Dimensions

Dimension - B Length inch	2.13 in
Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	108 mm
Dimension - Length BB inch	2.13 in
Dimension - Length Overall inch	4.25 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Run	1 IPS
Conductor - Copper Tube Std Size	1 IPS

Conductor - Copper Tube Std Size Range	1 IPS
Conductor - Copper Tube Std Tap	1 IPS
Conductor Type	CU Tube Std-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)