



OEM840NCP

by Burndy
Catalog ID: OEM840NCP

OEM Pneumatic Bench Press, 4.5 Tons Output, Operating Pressure 90 - 100 psi

- Customizable clear safety guard for left, right, or front feed cable entry
- Guarded foot switch
- Adjustable connector locator
- Cycle counter
- Accommodates UM, U and W dies
- Testing for UL Listing performed up to: U dies: UL Listed to 1/0 AWG (YA-L), #2 AWG(YAV-L), W dies: UL Listed to 3/0 AWG (YA-L), 1/0 AWG(YAV-L)

2 year limited warranty

Product Details

General

Crimp Force Capacity	4.5 ton
Die Type	U DIE
Tool Type	Pneumatic Press
Type	Crimpers
UPC	781810660379

Dimensions

Height	22.01 in
Length	18.56 in
Weight	61 lb
Width	10.26 in

Conductor Related

Crimping Ranges	Installs #8 - 4/0 AWG
-----------------	-----------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)