

# PAT444SL5DC

by Burndy  
Catalog ID: PAT444SL5DC

Prop 65 Notice

PATRIOT CRIMPER 11-TON, DIE-LESS 5.0AH, 18V LI

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation

C-Head, Dieless System with Range Taking Capability



## Product Details

### General

Application	Crimping
Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945484344

### Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 Kcmil; Aluminum: 4-1000 Kcmil; ACSR: #4 AWG-556.6 Kcmil
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)