

PAT444SL5

by Burndy
Catalog ID: PAT444SL5

Prop 65 Notice

CRIMPER 11-TON, DIE-LESS 5.0AH, Hydraulic Self Contained, 18V Lithium-Ion

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation

C-Head, Dieless System with Range Taking Capability



Product Details

General

Application	Crimping
Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945484351

Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 Kcmil; Aluminum: 4-1000 Kcmil; ACSR: #4 AWG-556.6 Kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)