

# PAT444SLCB

by Burndy  
Catalog ID: PAT444SLCB

Prop 65 Notice

11-Ton, Die less Nest and Indenter Crimper, Hydraulic Self Contained, 18V Lithium-Ion, No Charger or Batteries.

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Durable high impact formed carrying case provides superior protection and stores all accessories



## Product Details

### General

Application	Crimping
Battery Type	Lithium Ion
Crimp Force Capacity	11 ton
Tool Type	Battery Actuated Crimper
Type	Crimpers
UPC	621945524873

### Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Certifications and Compliance

Certification - ETL	No
---------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)