

PAT444SLIDC

by Burndy
Catalog ID: PAT444SLIDC

Prop 65 Notice

PATRIOT CRIMPER 11-TON, DIE-LESS 3.0AH, 18V LI

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation

C-Head, Dieless System with Range Taking Capability



Product Details

General

Application	Crimping
Battery Type	Lithium Ion
Crimp Force Capacity	11 ton
Sub Brand	PATRIOT® CRIMPER
Type	Crimpers
UPC	621945484337

Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)