

PAT444SLI

by Burndy
Catalog ID: PAT444SLI

Prop 65 Notice

PATRIOT 11-Ton C-Head Dieless Tool, 3.0Ah 18V Li-ion, 120V AC Charger

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation

C-Head, Dieless System with Range Taking Capability5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Recharge Time	0.5 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945474451
UPC 12 Digit	621945474451

Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 Kcmil; Aluminum: 4-1000 Kcmil; ACSR: #4 AWG-556.6 Kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (2) 3Ah 18V li-ion batteries, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)