

# PAT46CLWLS5

by Burndy  
Catalog ID: PAT46CLWLS5

Prop 65 Notice

15-Ton, Light Weight C-Head Crimper, Hydraulic Self-Contained, 18V Lithium-Ion, 5.0Ah, Rubber Covered Head

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Overmolded, ergonomic handle
- Improved ergonomic balance

Durable high impact formed carrying case provides superior protection and stores all accessories 5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE®



## Product Details

### General

Application	Crimping
Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADP1)
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945477728

### Dimensions

Height	12.88 in
Jaw Width	2 in
Length	18.44 in
Weight	18.9 lb
Width	3.26 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground rods: 1/2"-1" diameter
-----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No

Certification - cULus
-----------------------

No
----

## Logistics

Minimum Pack Quantity
-----------------------

1
---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)