



PAT46LW18V250V

by Burndy
Catalog ID: PAT46LW18V250V

Prop 65 Notice

Hydraulic Self Contained Battery Actuated tool 18V with 250V Charger, 15 Tons, 18 V Ni-MH

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Overmolded, ergonomic handle
- Improved ergonomic balance

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE®

Product Details

General

Battery Type	3.0 Ah Ni-MH
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADP1)
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810654811
UPC 12 Digit	7818106548111

Dimensions

Height	13.75 in
Jaw Width	2 in
Length	18.65 in
Weight	17.5 lb
Width	3.70 in

Conductor Related

Crimping Ranges	Copper:#AWG Str. - 1500 kcmil, Aluminum:#8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)