

## PAT46LWL5DC

by Burndy  
Catalog ID: PAT46LWL5DC

Prop 65 Notice

15-Ton, Light Weight Latch Head, Hydraulic Self-Contained with 12V Charger, 18V Lithium-Ion, 5.0Ah

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

5 YEAR LIMITED WARRANTY ON THE TOOL, 3 YEAR LIMITED WARRANTY ON THE BATTERIES AND CHARGER.



## Product Details

### General

|                      |                             |
|----------------------|-----------------------------|
| Battery Type         | 5.0 Ah Li-Ion               |
| Crimp Force Capacity | 15 ton                      |
| Die Type             | P and U style (with PUADP1) |
| Recharge Time        | 0.75 h                      |
| Tool Type            | Battery Actuated Crimper    |
| Trade Name           | PATRIOT®                    |
| Type                 | Crimpers                    |
| UPC                  | 621945470057                |

### Dimensions

|           |          |
|-----------|----------|
| Height    | 13.93 in |
| Jaw Width | 2 in     |
| Length    | 18.59 in |
| Weight    | 16.8 lb  |
| Width     | 3.26 in  |

### Electrical Ratings

|                   |        |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

### Conductor Related

|                 |   |
|-----------------|---|
| Crimping Ranges | Copper:#AWG Str. - 1500 kcmil, Aluminum:#8 AWG - 1250 kcmil |
|-----------------|---|

### Certifications and Compliance

|                               |    |
|-------------------------------|----|
| Certification - CSA Approved  | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)