

PAT46LWL5

by Burndy
Catalog ID: PAT46LWL5

Prop 65 Notice

PATRIOT 15-TON LATCH-HEAD CRIMPER, 5.0 AH LITHIUM-ION BATTERY.

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

2 inch jaw opening; Light weight; 355 degree head rotation; Ergonomically balanced
5 YEAR LIMITED WARRANTY ON THE TOOL, 3 YEAR LIMITED WARRANTY ON THE BATTERIES AND CHARGER.



Product Details

General

Application	Crimping
Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADP1)
Recharge Time	0.75 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945470620

Dimensions

Height	13.93 in
Jaw Width	2 in
Length	18.59 in
Weight	16.8 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil; Ground rods: 1/2"-1" diameter
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)