

PAT46LWLILCB

by Burndy
Catalog ID: PAT46LWLILCB

Prop 65 Notice

15-Ton, Light Weight Latch Head, Hydraulic Self-Contained Less Charger and Battery, 3.0Ah

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE®



Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADP1)
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810654798
UPC 12 Digit	7818106547988

Dimensions

Height	13.93 in
Jaw Width	2 in
Length	18.59 in
Weight	16.8 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI

UL Listed

No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)