



PAT46LWS18VDC

by Burndy
Catalog ID: PAT46LWS18VDC

15-Ton, Light Weight C-Head Crimper, Hydraulic Self-Contained with 12V Charger, 18V Ni-MH, 3.0Ah

- 2" jaw opening
- Used with P dies
- U dies with PUADPI adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Overmolded, ergonomic handle
- Improved ergonomic balance

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE®

Product Details

General

Battery Type	3.0 Ah Ni-MH
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADPI)
Recharge Time	0.5 h
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810672440
UPC 12 Digit	7818106724400

Dimensions

Height	13.75 in
Jaw Width	2 in
Length	18.44 in
Weight	19.7 lb
Width	3.70 in

Conductor Related

Crimping Ranges	Copper:#AWG Str. - 1500 kcmil, Aluminum:#8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)