

PAT46LWSL5DC

by Burndy
Catalog ID: PAT46LWSL5DC

Prop 65 Notice

15-Ton, Light Weight C-Head Crimper, Hydraulic Self-Contained with 12V Charger, 18V Li-Ion, 5.0Ah

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, scoop style C-head with 355° head rotation
- Overmolded, ergonomic handle
- Improved ergonomic balance

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE®



Product Details

General

Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADP1)
Recharge Time	0.75 h
Type	Crimpers
UPC	621945470071

Dimensions

Height	12.88 in
Jaw Width	2 in
Length	18.44 in
Weight	18.9 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper:#AWG Str. - 1500 kcmil, Aluminum:#8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)