



PAT4PC83418V250V

by Burndy
Catalog ID: PAT4PC83418V250V

Prop 65 Notice

4 point C-HEAD Crimping tool, 6-Ton, 18 V-DC

Product Details

General

Battery Type	Nickel Metal Hydride (NiMH)
Tool Type	Dieless
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810475614
UPC 12 Digit	7818104756144

Dimensions

Dimension - Height inch	13.9 in
Dimension - L Length Overall mm	447 mm
Dimension - Length Overall inch	17.6 in
Dimension - Width inch	3.7 in
Dimension - Width mm	94 mm

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)