



PAT4PC83418V

by Burndy
Catalog ID: PAT4PC83418V

Prop 65 Notice

6-Ton, 4-POINT® Dieless, C-Head Hydraulic self-Contained Battery Actuated Tool, 18V Ni-MH

- True one handed operation for advance, retract and hold function
- 360 degree head rotation
- Ergonomically balanced
- Dieless crimp technology
- Large handle grip with trigger guard

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE®

Product Details

General

Battery Type	Nickel Metal Hydride (NiMH)
Crimp Force Capacity	6 ton
Die Type	Dieless
Recharge Time	0.75 h
Tool Type	Dieless
Trade Name	4-POINT®
Type	Crimpers
UPC	781810456521
UPC 12 Digit	7818104565211

Dimensions

Height	13.9 in
Length	17.6 in
Width	3.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper:#8 - 1000 kcmil, Copper Flex:#8 - 777.7 kcmil, Aluminum:#8 - 750 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)