

# PAT500SJ68L5CUTKIT1

by Burndy  
Catalog ID: PAT500SJ68L5CUTKIT1

PATRIOT® 6-Ton, Scissor Action Hydraulic Self-Contained Tool Kit that includes crimp head with O & D3 grooves, cutter jaw, 120V charger and 2 batteries (5.0Ah)

- Interchangeable scissor action crimping and cutting jaws
- 180° head rotation
- Uses W and X style dies
- Ergonomically balanced tool design

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger



## Product Details

### General

Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W and X ( O and D3 Groove Crimp Head)
Recharge Time	0.75 h
Tool Type	Battery Actuated Scissor Action Tool Kit
Trade Name	PATRIOT®
Type	Cutters
UPC	621945477797

### Dimensions

Height	13.4 in
Length	16.8 in
Weight	11 lb
Width	2.9 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Taps-Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups-#6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals-#10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations-#8 to 500 kcmil Copper Stranded (YA, YA-L, YS, YS-L), #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum (YA-A, YS-A)
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)