

PAT500SJ6L5CUTKIT1

by Burndy
Catalog ID: PAT500SJ6L5CUTKIT1

PATRIOT® 6-Ton PAT500SJ6L5 tool, Scissor Action Kit that includes crimp head with BG & D3 grooves, cutter jaw, 120V charger and 2 batteries (5.0Ah)

- Interchangeable scissor action crimping and cutting jaws
- 180° head rotation
- Uses W and X style dies
- Ergonomically balanced tool design

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger



Product Details

General

| | |
|----------------------|--|
| Battery Type | 5.0 Ah Li-Ion |
| Crimp Force Capacity | 6 ton |
| Die Type | W and X (BG and D3 Grooves) |
| Recharge Time | 0.75 h |
| Tool Type | Battery Actuated Scissor Action Tool Kit |
| Trade Name | PATRIOT® |
| Type | Cutters |
| UPC | 621945477780 |

Dimensions

| | |
|--------|---------|
| Height | 13.4 in |
| Length | 16.8 in |
| Weight | 11 lb |
| Width | 2.9 in |

Electrical Ratings

| | |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | Taps-Copper: #10 sol. to 2/0 str., Aluminum & ACSR: #14 sol. to 4/0 ACSR; Stirrups-#6 to 4/0 ACSR; Overhead Full Tension Deadends, Full Tension Splices and Terminals-#10 str. to 4/0 ACSR; Installs Splices, Taps or Terminations-#8 to 500 kcmil Copper Stranded (YA, YA-L, YS, YS-L), #8 to 350 kcmil Copper Flex, #8 to 350 kcmil Aluminum (YA-A, YS-A) |
|-----------------|---|

Certifications and Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

Logistics

| |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

| |
|---|
| 1 |
|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)