



PAT600C18V

by Burndy
Catalog ID: PAT600C18V

Prop 65 Notice

6 Ton, Latch Head Battery Actuated Tool, Hydraulic self-Contained, 18V Ni-MH, 110 V AC Charger with Covered Head

- Specialized latch head design
- Ergonomic design allows one hand operation for Ram advance and Ram retraction
- 180 degree head rotation
- Permanent D3 crimp groove accepts all W Dies
- Enhanced clearance for tap connections

5 Year Limited Warranty on Tool, 1 Year on Batteries and Charger

Product Details

General

Battery Type	Nickel Metal Hydride (NiMH)
Crimp Force Capacity	6 ton
Die Type	W, V, W-VT style dies
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810363584
UPC 12 Digit	7818103635844

Dimensions

Height	13.75 in
Length	14.5 in
Weight	10.9 lb
Width	3.5 in

Conductor Related

Crimping Ranges	#8 - 600 kcmil Copper Str. (YA, YA-L, YS, YS-L), #8 - 350 kcmil Flex, #8 - 350 kcmil Aluminum (YA-A & YS-A)
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)