



## PAT600CL5

by Burndy  
Catalog ID: PAT600CL5

Prop 65 Notice

6 Ton, Latch Head Battery Actuated Tool, Hydraulic self-Contained, 18V Li-Ion 5.0Ah Battery, 120 V AC Charger with Covered Head

- Specialized latch head design
- Ergonomic design allows one hand operation for Ram advance and Ram retraction
- 180 degree head rotation
- Permanent D3 crimp groove accepts all W Dies
- Enhanced clearance for tap connections

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE

## Product Details

### General

Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W, V, W-VT style dies
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945477803

### Dimensions

Height	13.7 in
Length	14.5 in
Weight	10.1 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	#8 - 600 kcmil Copper Str. ( YA, YA-L, YS, YS-L), #8 - 350 kcmil Flex, #8 - 350 kcmil Aluminum (YA-A & YS-A)
-----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)