



PAT600CLI

by Burndy
Catalog ID: PAT600CLI

Prop 65 Notice

6 Ton, Latch Head Battery Actuated Tool, Hydraulic self-Contained, 18V Li-Ion 3.0Ah Battery, 120 V AC Charger with Covered Head

- Specialized latch head design
- Ergonomic design allows one hand operation for Ram advance and Ram retraction
- 180 degree head rotation
- Permanent D3 crimp groove accepts all W Dies
- Enhanced clearance for tap connections

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W, X, W-VT style dies
Recharge Time	0.5 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810512913
UPC 12 Digit	7818105129133

Dimensions

Height	13.7 in
Length	14.5 in
Weight	10.1 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG-600 Kcmil; Copper Flex: #8 AWG-350 Kcmil Flex; Aluminum: #8 AWG-350 Kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)