

PAT644L5

by Burndy
Catalog ID: PAT644L5

Prop 65 Notice

PATRIOT 11-TON ONE-CRIMP DIELESS CRIMPER, 5.0 AH LITHIUM-ION BATTERY.

- Dieless system eliminates the need to purchase and maintain dies
- Dieless system allows connectors and splices to become range taking
- 355° head rotation
- Ergonomically balanced

Dieless system, Range taking capabilities, 355° head rotation, 5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Crimping
Battery Type	5.0 Ah Li-Ion
Die Type	Dieless
Recharge Time	0.75 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945470972

Dimensions

Height	14.1 in
Length	15.6 in
Weight	15.9 lb
Width	3.2 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #6 AWG - 1000 kcmil; Aluminum: #6AWG - 900 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)