



PAT644LI

by Burndy
Catalog ID: PAT644LI

Prop 65 Notice

Battery Actuated Crimping Tool, Hydraulic Self Contained, 11 Ton Output Force, 6 AWG-1000 kcmil Copper, 6 AWG-750 kcmil Aluminium, Dieless, 18V Lithium Ion.

- Dieless system eliminates the need to purchase and maintain dies
- Dieless system allows connectors and splices to become range taking
- 355° head rotation
- Ergonomically balanced

Overmolded handle for comfort and improved grip, allows for one-handed operation for advance, retract and hold, 18-volt Lithium-Ion batteries provide 2.5 times more charge/discharge cycles than traditional Ni-Cd batteries and provide 430 percentage more life time work 5 Year Limited Warranty on Tool, 3 Year on Batteries and 1 year warranty on the Charger

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Recharge Time	0.5 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810505489
UPC 12 Digit	7818105054899

Dimensions

Height	14.1 in
Length	15.6 in
Weight	15.9 lb
Width	3.2 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #6 AWG - 1000 kcmil; Aluminum: #6AWG - 900 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)