

# PAT750L5DC

by Burndy  
Catalog ID: PAT750L5DC

Prop 65 Notice

12-Ton, C-Head Crimper, 12V DC Charger, 18V Li-Ion, 5.0Ah

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger,  
Lifetime Warranty on INFINITY DRIVE®



## Product Details

### General

Application	Crimping
Battery Type	5.0 Ah Li-Ion
Die Type	U DIE
Recharge Time	0.75 h
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	621945471009

### Dimensions

Height	13.5 in
Length	15.7 in
Weight	15.7 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground rods: 1/2"-1" diameter.
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)