



PATCUT129AR18V250V

by Burndy
Catalog ID: PATCUT129AR18V250V

Prop 65 Notice

Latch Head, Battery Actuated Cutting Tool, Hydraulic Self Contained, Cu/Al 1.29" (Max), 1113 ACSR(Max), 5/8" Ground Rod, 18V Ni-MH, 250V AC Charger

- Special Latch head design provides interference free closure for Mid-Span cuts
- 180° head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold
- Durable high impact carrying case

5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Battery Type	2.6 Ah Ni-MH
Crimp Force Capacity	7 ton
Die Type	Dieless
Recharge Time	0.75 h
Tool Type	Battery Actuated Cutting Tool
Trade Name	PATRIOT®
Type	Cutters
UPC	781810370797
UPC 12 Digit	7818103707977

Dimensions

Height	12.80 in
Length	14.5 in
Weight	12.0 lb
Width	3.7 in

Electrical Ratings

Operating Voltage	18V DC
-------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)