

PATCUT129L5DC

by Burndy
Catalog ID: PATCUT129L5DC

Prop 65 Notice

Latch Head, ACSR up to 1113 kcmil Hydraulic Self Contained Battery Actuated tool 18V Cutter with 120V DC Charger, 18 V 5.0Ah Li-Ion

5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



Product Details

General

Application	Cutting
Battery Type	5.0 Ah Li-Ion
Recharge Time	0.75 h
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	621945471047

Dimensions

Height	13.5 in
Length	14.5 in
Weight	10.2 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum Cable: upto 1.29"; ACSR: upto 1113 Kcmil; Ground rod: upto 5/8"; Rebar: upto 1/2"; Soft steel bolts: upto 5/8"; Standard Guy: upto 1/2"; EHS Guy: upto 3/8"
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)