

# PATCUT129L5

by Burndy  
Catalog ID: PATCUT129L5

Prop 65 Notice

PATRIOT 1.29" ACSR LATCH-HEAD CUTTER, 5.0 AH LITHIUM-ION BATTERY.

REFINED HYDRAULIC SYSTEM FOR ULTRA PERFORMANCE, SPEED AND RELIABILITY; FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS; 180 degree Head rotation; MECHANICAL RAM RELEASE: PROVIDES CONSISTENT, RELIABLE RAM RETRACTION,(NO BATTERY POWER CONSUMPTION)5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



## Product Details

### General

Application	Cutting
Battery Type	5.0 Ah Li-Ion
Recharge Time	0.75 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	621945471030

### Dimensions

Height	13.5 in
Length	14.5 in
Weight	10.2 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum Cable: upto 1.29"; ACSR: upto 1113 Kcmil; Ground rod: upto 5/8"; Rebar: upto 1/2"; Soft steel bolts: upto 5/8"; Standard Guy: upto 1/2"; EHS Guy: upto 3/8"
-----------------	---

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)