



PATMD14605A1

by Burndy
Catalog ID: PATMD14605A1

IN-LINE® Tool, crimping jaw (BG/D3 grooves); ACSR & GUY cutting jaws; two (2) Makita 5.0Ah Batteries; 120 V AC Charger

- Lightweight, compact and ergonomic design
- Interchangeable scissor action crimping and cutting jaws
- Safety trigger lock and locking jaw tabs
- LED Worklight
- EP Enhanced Power tools accept 2.0, 3.0, 4.0, 5.0, and 6.0Ah Makita batteries

Product Details

General

Application	Crimping and Cutting
Battery Type	5.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W Dies
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimpers & Cutters
UPC	621945546592

Dimensions

Height	2.75 in
Length	19.25 in
Weight	7.2 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping Capacity: Copper: #8 AWG - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil; AAC: #14 AWG - 350 kcmil; ACSR: #14 - 4/0 AWG; Cutting Capacity: ACSR: 556.5 (26/7); EHS Guy: 3/8"
-----------------	--

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)