



PATMD66LW5WCCJ

by Burndy
Catalog ID: PATMD66LW5WCCJ

Tool, crimping jaw (D3 groove); cutting jaw with CU/AL blades; 2 Makita 5.0Ah Batteries; 120 V AC Charger

- Compact Size - Reduced weight and length
- Robust Jaw Design — Improves tool balance and user experience
- Interchangeable scissor or action crimping and cutting jaws
- 350° Rotatable Head — Allows the tool to be used in multiple positions for hard to reach areas
- LED Worklight — Lights up the work area in dimly lit spaces
- LIFETIME WARRANTY ON INFINITY DRIVE MOTOR AND TRANSMISSION
- 5-YEAR LIMITED WARRANTY (EXCLUDING BLADES)

Product Details

General

Application	For Crimping: Copper: #8 AWG - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum (AAC): #14 AWG - 350 kcmil, ACSR: #14 - 4/0 AWG and For Cutting: Soft Drawn Copper up to 500 kcmil and Aluminum up to 636 kcmil
Type	Cutters
UPC	621945528758

Dimensions

Height	2.75 in
Length	17.85 in
Weight	9.2 lb
Width	4.375 in

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)