



## PATMD66LWWCCJ

by Burndy  
Catalog ID: PATMD66LWWCCJ

Tool, crimping jaw (D3 groove); cutting jaw with CU/AL blades; 2 Makita 3.0Ah Batteries; 120 V AC Charger

- Compact Size - Reduced weight and length
- Robust Jaw Design — Improves tool balance and user experience
- Interchangeable scissor or action crimping and cutting jaws
- 350° Rotatable Head — Allows the tool to be used in multiple positions for hard to reach areas
- LED Worklight — Lights up the work area in dimly lit spaces
- LIFETIME WARRANTY ON INFINITY DRIVE MOTOR AND TRANSMISSION
- 5-YEAR LIMITED WARRANTY (EXCLUDING BLADES)

## Product Details

### General

Application	For Crimping: Copper: #8 AWG - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum (AAC): #14 AWG - 350 kcmil, ACSR: #14 - 4/0 AWG and For Cutting: Soft Drawn Copper up to 500 kcmil and Aluminum up to 636 kcmil
Type	Cutters
UPC	621945528727

### Dimensions

Height	2.75 in
Length	17.85 in
Weight	9.2 lb
Width	4.375 in

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)