



PATMD68LW5DC

by Burndy
Catalog ID: PATMD68LW5DC

Prop 65 Notice

PATRIOT® IN-LINE® 6 Ton Light Weight Crimper, Permanent O and D3 Grooves, two (2) 5.0AH Li-Ion batteries, 18V DC Charger, Lanyard, Utility Bag

Multi-AH Capability: Accepts 2.0AH, 3.0AH, 4.0AH, and 5.0AH Makita batteries.

Warranty: Lifetime on INFINITY DRIVE®, 5-year limited on tool, 3-year on batteries and charger

Product Details

General

Die Type	Accommodates W-Dies
Trade Name	PATRIOT® IN-LINE®
Type	Crimpers
UPC	621945477131

Dimensions

Height	2.75 in
Length	18.73 in
Weight	6.7 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 500 kcmil Copper Flex: #8 AWG - 350 kcmil Aluminum (AAC): #14 AWG - 350 kcmil ACSR: #14 - 4/0 AWG
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)