



PATMD6LW5WCCJ

by Burndy
Catalog ID: PATMD6LW5WCCJ

Tool, crimping jaw (BG/D3 grooves); cutting jaw with CU/AL blades; 2 Makita 5.0Ah Batteries; 120 V AC Charger

- Compact Size - Reduced weight and length
- Robust Jaw Design — Improves tool balance and user experience
- Interchangeable scissor or action crimping and cutting jaws
- 350° Rotatable Head — Allows the tool to be used in multiple positions for hard to reach areas
- LED Worklight — Lights up the work area in dimly lit spaces
- LIFETIME WARRANTY ON INFINITY DRIVE MOTOR AND TRANSMISSION
- 5-YEAR LIMITED WARRANTY (EXCLUDING BLADES)

Product Details

General

| | |
|-------------|---|
| Application | For Crimping: Copper: #8 AWG - 500 kcmil, Copper Flex: #8 AWG - 350 kcmil, Aluminum (AAC): #14 AWG - 350 kcmil, ACSR: #14 - 4/0 AWG and For Cutting: Soft Drawn Copper up to 500 kcmil and Aluminum up to 636 kcmil |
| Type | Cutters |
| UPC | 621945528734 |

Dimensions

| | |
|--------|----------|
| Height | 2.75 in |
| Length | 18.70 in |
| Weight | 9.2 lb |
| Width | 4.375 in |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)