



PATMD6LW5WCJ

by Burndy
Catalog ID: PATMD6LW5WCJ

Prop 65 Notice

Patriot inline 6-ton crimper with d3 and bg grooves and cutter jaw 5.0 ah, 18v li-ion battery 120v charger.

Tool, Crimping jaw with D3 and BG grooves, 5.0 Ah Batteries, 120 V AC charger

Product Details

General

Application	Crimping and Cutting
Battery Type	5.0 Ah Li-Ion
Die Type	W Dies
Sub Brand	PATRIOT® IN-LINE® CRIMP/CUT KIT
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimpers & Cutters
UPC	621945480919

Dimensions

Height	2.75 in
Length	18.70 in
Weight	9.2 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping Capacity: Copper: #8 AWG - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; AAC: #14 AWG - 350 kcmil; ACSR: #14 - 4/0 AWG; Cutting Capacity: ACSR: upto 556.5 kcmil (26/7)
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)