



PATMD6LWWCJ

by Burndy
Catalog ID: PATMD6LWWCJ

Prop 65 Notice

IN-LINE® Tool, crimping jaw (BG/D3 grooves) ACSR cutting jaw, two (2) Makita 3.0Ah Batteries, 120V AC Charger

- Lightweight, compact and ergonomic design
- Interchangeable scissor action crimping and cutting jaws
- Safety trigger lock and locking jaw tabs
- LED Worklight
- EP Enhanced Power tools accept 2.0Ah - 6.0Ah 18V Lithium-ion Makita batteries

Tool, Crimping jaw with D3 and BG grooves, 3.0 Ah Batteries, 120 V AC charger, 5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	Crimping and Cutting
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W Dies
Recharge Time	0.5 h
Sub Brand	PATRIOT® IN-LINE® CRIMP/CUT KIT
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimpers & Cutters
UPC	621945480933
UPC 12 Digit	621945480933

Dimensions

Height	2.75 in
Length	18.70 in
Weight	9.2 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping Capacity: Copper: #8 AWG - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; AAC: #14 AWG - 350 kcmil; ACSR: #14 - 4/0 AWG; Cutting Capacity: ACSR: upto 556.5 kcmil (26/7)
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, BG/D3 crimp jaw, ACSR cut jaw, (2) 3Ah Li-ion batteries, charger, wrist strap and utility bag

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)