



PATMDCUTLWJAW

by Burndy
Catalog ID: PATMDCUTLWJAW

Prop 65 Notice

6T IN-LINE® CUTTER JAW, ACSR/AL/CU (JAW ONLY)

- Interchangeable scissor action cutting jaw
- Locking jaw tabs

Cutting Jaw (CU/AL/ACSR blades)

Product Details

General

Application	Cutting
Crimp Force Capacity	6 ton
Recharge Time	0.5 h
Sub Brand	PATRIOT® IN-LINE® CUTTER JAW
Tool Type	Cutter Jaw
Trade Name	PATRIOT®
Type	Cutters
UPC	621945483460
UPC 12 Digit	621945483460

Dimensions

Height	1.375 in
Length	5.82 in
Weight	2.5 lb
Width	4.58 in

Conductor Related

Crimping Ranges	Cutting Capacity: ACSR (26/7) 556.5 kcmil; AAC 636 kcmil; Copper: 350 Kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Jaw only

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)