



## PENA13CARTRIDGE

by Burndy  
Catalog ID: PENA13CARTRIDGE

Cartridge for PENETROX A-13.

Features: PENETROX A-13 Consists Of A Nonpetroleum Base Vehicle In Which Zinc Particles Are Suspended, Recommended For Aluminum To Aluminum, Aluminum To Copper Applications And Aluminum Conduit Threads, Compatible With Insulating Materials Such As Rubber, Or Polyethylene, UL Listed And Recommended For All Voltages, Dropping Point (minimum): 500 DEG F, Pour Point(maximum): -10 DEG F, Penetration (unworked): 250 In Accordance To ASTM D217 Indicates The Consistency Of A Grease, Container Consist Of: Non - Petroleum Base Vehicle In Which Zinc Particles Are Suspended

## Product Details

### General

|   |   |
|---|---|
| Application                             | For Aluminum To Copper, Aluminum To Aluminum, Aluminum To Conduit |
| Application - For Use On                | Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper       |
| Container Type                          | Cartridge   |
| Pour Point                              | -40 °F  |
| Sub Brand                               | PENETROX  |
| Temperature - Dropping Point Fahrenheit | 350 °F  |
| Trade Name                              | PENETROX™   |
| Type                                    | A13   |
| UPC                                     | 781810365519  |
| UPC 12 Digit                            | 7818103655199   |
| Viscosity at 100 Fahrenheit             | 250 °F  |

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | No  |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

### Logistics

|                       |      |
|-----------------------|------|
| Container Size        | 1 lb |
| Minimum Pack Quantity | 1    |

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)

